
# Eaton CHP14B100R

## Catalog Number: CHP14B100R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 100 A, X0, Copper, NEMA 3R, Metallic, CH, 28, 14, Three-wire, Single-phase, Overhead, 120/240 V





Eaton CH main breaker loadcenter

UPC

786689058517

**Product Height** 

5.19 in

**Product Weight** 

18 lb

Certifications

UL 50 UL 67 Catalog Number

CHP14B100R

Product Length/Depth

16.75 in

**Product Width** 

14.31 in

Warranty

Limited lifetime

#### Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.





## default Taxonomy Attribute Label

#### Special features

Cover included

Type

Main breaker

Amperage Rating

100 A

Bus material

Copper

Main circuit breaker

СН

Number of circuits

28

Number of spaces

14

Phase

Single-phase

Feed type

Overhead

Voltage rating

120/240 V

Box size

X0

Enclosure

NEMA 3R

**Enclosure material** 

Metallic

Number of wires

3

### Resources

#### **Brochures**

Loadcenters and Circuit Breakers

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CHP14B100R



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia