



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CVX050240H CVX050-240H Efa Asm *Eaton Power Quality*

Catalog Number	CVX050240H
Manufacturer	Eaton Power Quality
Description	Surge Protection Device, CVX050 Series, 50 Kaic, 240V, 480V, 600V, 300 L-L, 150 L-N, 150 L-G, 640 N-G Operating Voltage, Three-Phase
Weight per unit	2.0 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

dimensions	3.5500 IN X 4.7500 IN X 5.6700 IN
Phase	Three-phase
Voltage Rating	240 V, 480 V, 600 V

Dimensions and Weight

Depth	3.5500
Height	5.6700
Width	4.7500

Descriptions

Description	CVX050-240H EFA ASM
extra long description	ETN CVX050-240H Eaton CVX surge pro
Features	Eaton's CVX050 and CVX100 Surge Protective Devices (SPDs) ensure that a customer's investment in equipment and processes are protected from the damaging effects of voltage transients. Designed for installation on service entrance, branch panels, or individual equipment disconnects, the CVX series provides enhanced surge protection for mission-critical applications. Available in configurations and current capacities of 50 or 100 kA per phase.
Long Description	Surge Protection Device, CVX050 series, 50 kAIC, 240V, 480V, 600V, 300 L-L, 150 L-N, 150 L-G, 640 N-G operating voltage, Three-phase
Product Type	Eaton CVX Surge Protection Device

Manufacturer Information

Brand	Eaton
GTIN	00786685514642
Manufacturers Part Number	CVX050-240H
UPC	786685514642

Taxonomies, Classifications, and Categories

Category Description	SURGE SUPRESSION PRODUCTS
Type	Surge protection device



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	2

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
standard	UL 1449