

Eaton CHP22B100X2

Catalog Number: CHP22B100X2

Eaton CH main breaker loadcenters, PON, Main breaker, 100 A, X2, Copper, X2, NEMA 1, Metallic, 10 kAIC, CH, 44, 22, Three-wire, Single-phase, #6-1/0 AWG, 120/240 V



Photo is representative

General specifications

| | |
|----------------------------------|-----------------------------------|
| Product Name | Catalog Number |
| Eaton CH main breaker loadcenter | CHP22B100X2 |
| UPC | Product Length/Depth |
| 786679189559 | 21 in |
| Product Height | Product Width |
| 3.88 in | 14.31 in |
| Product Weight | Warranty |
| 12.3 lb | Limited lifetime |
| Certifications | Catalog Notes |
| UL 67 | Purchase Size X2 Cover Separately |
| UL 50 | |

defaultTaxonomyAttributeLabel

Special features

PON

Type

Main breaker

Amperage Rating

100 A

Bus material

Copper

Cover

X2

Main circuit breaker

CH

Number of circuits

44

Number of spaces

22

Phase

Single-phase

Wire size

#6-1/0 AWG

Voltage rating

120/240 V

Box size

X2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP22B100X2](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CHP22B100X2

Catalog Number: CHP22B100X2

Eaton CH main breaker loadcenters, PON, Main breaker, 100 A, X2, Copper, X2, NEMA 1, Metallic, 10 kAIC, CH, 44, 22, Three-wire, Single-phase, #6-1/0 AWG, 120/240 V



Photo is representative

General specifications

| | |
|----------------------------------|-----------------------------------|
| Product Name | Catalog Number |
| Eaton CH main breaker loadcenter | CHP22B100X2 |
| UPC | Product Length/Depth |
| 786679189559 | 21 in |
| Product Height | Product Width |
| 3.88 in | 14.31 in |
| Product Weight | Warranty |
| 12.3 lb | Limited lifetime |
| Certifications | Catalog Notes |
| UL 67 | Purchase Size X2 Cover Separately |
| UL 50 | |

defaultTaxonomyAttributeLabel

Special features

PON

Type

Main breaker

Amperage Rating

100 A

Bus material

Copper

Cover

X2

Main circuit breaker

CH

Number of circuits

44

Number of spaces

22

Phase

Single-phase

Wire size

#6-1/0 AWG

Voltage rating

120/240 V

Box size

X2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP22B100X2](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)