

Straight Ceiling Wire Galvanized

Catalog# CW1212

12 Gauge x 12 Foot Straight Ceiling Wire

Section Table Of Contents Div. 09 – Finishes Section 09510 Acoustical Ceilings

2.3.1 – Wires Shall Conform To ASTM A641/A 641M

American Standard Wire Gauges For Steel - 12 GageDiameter Inches:.1055" (+/- .003)Diameter (mm):2.680LBS Per 1000 FT:29.476Feet Per LB:33.618Area (in2):0.008742

Performance Data – 12 Gauge Wire	
Typical 3 Wrap Tie Per ASTM C636	270 LBS (Wire Tie Failure/Pullout Load)
Tight 3 Wrap Tie	358 LBS (Wire Tie Failure/Pullout Load)
Yields	424 LBS (Wire Tie Failure/Pullout Load)
Ultimate Load	550 LBS
Tensile Strength	75 KSI Max

Splice Options – Hanger wire splices are typical when the ceiling drop is greater than the length of the wire available and are allowed in seismic ceiling construction. The industry standard is to loop and tie the wire ends with three tight turns, or use a square knot. The square knot is the stronger of the two options at 550 LBS versus 350 LBS for the loop and tie option.

Peco Fasteners specification sheets are a reference guide to help in the selection of fasteners. Peco has made every effort to ensure the accuracy of the information. However, Peco Fasteners is not responsible for any errors that may be contained within these sheets. Peco Fasteners makes no claim of warranty in the accuracy of this information. Users of this information are solely responsible for protecting themselves against liability. It is the solely the responsibility of the purchasers and users of this material to consult with Engineers that are experts in an applicable field. Peco Fasteners is not responsible for any loss, claim, or damage due to these specification sheets.