



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

427 Metro Park Drive
75071-0000, TX McKinney
Phone: 972-542-1196
Fax: 972-542-2279



CHP22B125R CH Pon Loadcntr 125A Main BRKR 22 Space N3R *Eaton Corp*

Catalog Number	CHP22B125R
Manufacturer	Eaton Corp
Description	Eaton CH Main Breaker Loadcenters, Cover Included, Main Breaker, 125 A, X2, Copper, Nema 3R, Metallic, CH, 44, 22, Three-Wire, Single-Phase, Overhead, 120/240 V
Weight per unit	23.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	125
media	Yes
number of spaces	22
Phase	1
Voltage Rating	120/240 V

Dimensions and Weight

Depth	21
Height	5.19
Size	X2
Width	14.31

Descriptions

Description	CH PON LOADCNTR 125A MAIN BRKR 22 SPACE N3R
extra long description	ETN CHP22B125R CH PON LC, 125A, MB,
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main breaker loadcenters,Cover included,Main breaker,125 A,X2,Copper,NEMA 3R,Metallic,CH,44,22,Three-wire,Single-phase,Overhead,120/240 V
Product Type	CH Pon LC, 125A, MB, 22SP, N3R
Special Features	Cover included



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

427 Metro Park Drive
75071-0000, TX McKinney
Phone: 972-542-1196
Fax: 972-542-2279

Manufacturer Information

Brand	Eaton
GTIN	00786689058579
Manufacturers Part Number	CHP22B125R
UPC	786689058579

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main breaker loadcenter

Packaging

Carton	1
Weight Per each	23

Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL 67,UL 50