

# Eaton CHP30B100X5

Catalog Number: CHP30B100X5

Eaton CH main breaker loadcenters, PON, Main breaker, 100 A, X5, Copper, X5, NEMA 1, Metallic, 10 kAIC, CH, 60, 30, Three-wire, Single-phase, #6-1/0 AWG, 120/240 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main breaker loadcenter	CHP30B100X5
<b>UPC</b>	<b>Product Length/Depth</b>
786679189597	29 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
15.6 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 50 UL 67	Purchase Size X5 Cover Separately

## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

Main breaker

### Amperage Rating

100 A

### Bus material

Copper

### Cover

X5

### Main circuit breaker

CH

### Number of circuits

60

### Number of spaces

30

### Phase

Single-phase

### Wire size

#6-1/0 AWG

### Voltage rating

120/240 V

### Box size

X5

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP30B100X5](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)