



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



D10250D Female Spon 12-10 Non-IP *Panduit Corporation*

| | |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | D10250D |
| Manufacturer | Panduit Corporation |
| Description | The Vibration Resistant Female Disconnect In Metallic Brass Helps Overcome The Failures Caused By High Vibration. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 12-10 Awg (4.0-6.0 MM ²). It Is 0.72"(18.3 MM) Long and 0.3" (7.6 MM) Wide. The Disconnect Is Non-Insulated, Is Tin-Plated, Has A Standard Barrel Configuration and A Sleeved Barrel. It Comes In A Boxes Of 500. |
| Weight per unit | 1.7 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|---------------|
| connection | Standard |
| insulation | Non-Insulated |
| Material | Brass |
| Voltage Rating | 2000 |
| Wire Size | #10 |

Material, Color, and Finish

| | |
|--------|------------|
| Finish | Tin-Plated |
|--------|------------|

Descriptions

| | |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | FEMALE SLPON 12-10 NON-IP |
| extra long description | PAN D10-250-D Pan-Term® D10-250-D L |
| Long Description | The vibration resistant female disconnect in metallic brass helps overcome the failures caused by high vibration. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 12-10 AWG (4.0-6.0 mm ²). It is 0.72"(18.3 mm) long and 0.3" (7.6 mm) wide. The disconnect is non-insulated, is tin-plated, has a standard barrel configuration and a sleeved barrel. It comes in a boxes of 500. |
| Product Type | Pan-Term® D10-250-D Loose Piece Disconnect |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983822058 |
| Manufacturers Part Number | D10-250-D |
| UPC | 074983822058 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description SPLIT BOLTS

Type Disconnect

Packaging

Carton 500

Weight Per each 1.68

Uses, Certifications, and Standards

Mounting 1932-09-01

standard UL Recognized, UL Listed 20H3 E78522; CSA Certified LR31212

Temperature Rating 302 Degrees Fahrenheit (150 Degrees Celsius)