



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6 South Hickory
71373-0000, LA Vidalia
Phone: 318-336-5113
Fax: 318-336-5587



CHP32L150X5 CH Pon Loadcncr 150A Mlo 32 Spaces

Eaton Corp

Catalog Number	CHP32L150X5
Manufacturer	Eaton Corp
Description	Eaton CH Main Lug Loadcenters, Pon, CH, 150 A, X5, Copper, !, Nema 1 Indoor, Steel, 25 Kaic, 64, 32, 3, Single-Phase, 120/240 V, #4 Awg-300 Kcmil
Weight per unit	16.8 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

Features

amperage rating	150
interrupt rating	25
media	Yes
number of spaces	32
Phase	1
Voltage Rating	120/240 V

Dimensions and Weight

Depth	29
Height	4
Size	X5
Width	14.3

Descriptions

Description	CH PON LOADCNCR 150A MLO 32 SPACES
extra long description	ETN CHP32L150X5 CH PON Loadcenter,
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main lug loadcenters, PON, CH, 150 A, X5, Copper, !, NEMA 1 indoor, Steel, 25 kAIC, 64, 32, 3, Single-phase, 120/240 V, #4 AWG-300 kcmil
Product Type	CH Pon Loadcenter, 150A, Mlo, 32 Spaces
Special Features	PON



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6 South Hickory
71373-0000, LA Vidalia
Phone: 318-336-5113
Fax: 318-336-5587

Manufacturer Information

Brand	Eaton
GTIN	00786689054298
Manufacturers Part Number	CHP32L150X5
UPC	786689054298

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main lug loadcenter

Packaging

Carton	1
Weight Per each	16.8

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL 67