

Eaton DG1-34170FN-C21C

Catalog Number: DG1-34170FN-C21C

Eaton PowerXL DG1 variable frequency drive, 380-500V input 90 kW 125 Hp CT 3PH 50/60 Hz 170A output IP21/type 1 enclosure FR6 LCD Internal EMC filter and DC choke EtherNet, RS-485, BACnet MS/TP, Modbus TCP and RTU ports 2 exp slots



General specifications

Product Name	Catalog Number
Eaton PowerXL DG1 variable frequency drive	DG1-34170FN-C21C
	UPC
	786685878850
Product Length/Depth	Product Height
44 in	20 in
Product Width	Product Weight
18 in	186 lb
Warranty	Compliances
Eaton Selling Policy 25-000 generally applies with some exceptions. Drive products come with a standard 24 months from date of shipment and 36 months with Eaton certified start up all inclusive coverage parts labor and travel.	C-Tick Compliant RoHS Compliant CE Marked GoST-R
	Certifications
	UL 508C EN 61800-5-1 IEC 61508 EN 62061 EN ISO 13849-1 EN 61800-3 cUL Listed UL Listed

defaultTaxonomyAttributeLabel

Brake chopper

No brake chopper

Horsepower

125 hp

Phase

Three-phase in, three-phase out

Frequency rating

50-60 Hz

Frame size

6

Keypad

Included

Input voltage

400 V, 380-500 V(-15%, +10%)

Display

LCD graphical

Torque rating

CT

Communication

EtherNet, RS-485, BACnet MS/TP, Modbus TCP and RTU communication

Enclosure

IP21/type 1

Input output

460 Vac (380-500 Vac, -15%, +10%)

Protection

Internal EMC filter, DC choke

Output current - max

170 A

Software

Active energy control, quick start wizard

Number of slots

2 expansion slots

Material

Coated board

Resources

Application notes

[Load balancing in multi motor applications](#)

[Operating at low temperatures](#)

[Digital I/Os](#)

[Connecting drives to generator supplies](#)

[Analog I/Os](#)

[PID controller](#)

[Smoke Mode and fire mode](#)

[Torque control](#)

[DG1 in pump and fan applications](#)

[Starting, stopping and operation](#)

[Dual Rating What exactly does that mean?](#)

[Electromagnetic compatibility \(EMC\)](#)

[Real time clock and use of the timers](#)

[Motor data and V/f curves](#)

Catalogs

[Data sheet](#)

[Product Range Catalog Drives Engineering](#)

[Eaton's Volume 6—Solid-State Motor Control](#)

Drawings

[DG1_FN_\(FR5-UL\) 3D Inventor](#)

[DG1_FN_\(FR5-UL\) 2D PDF](#)

[DG1_FN_\(FR5-UL\) 2D Drawing Xchange](#)

[DG1_FN_\(FR5-UL\) AutoCAD 2D Footprint \(mm\)](#)

[DG1_FN_\(FR5-UL\) AutoCAD 2D Footprint](#)

[DG1_FN_\(FR5-UL\) 3D Model Xchange](#)

Installation instructions

[PowerXL DG1 Series VFD Application Manual](#)

[PowerXL DG1 Series VFD Installation Manual](#)

Multimedia

[PowerXL DG1 Variable Frequency Drive - Setup via WebUI](#)

[Power XL General Purpose Drives](#)

Specifications and datasheets

[Eaton Specification Sheet - DG1-34170FN-C21C](#)

Warranty guides

Power consumption

90 kW

Electromagnetic compatibility filter

EMC Filter

Internal DC choke

Yes

Conformal coated boards

Yes

User interface

Graphical Keypad

High overload (CT) amps

170 A

High overload (CT) kW

90 kW

High overload (CT) hp

125 hp

Low overload (VT) amps

205 A

Low overload (VT) kW

110 kW

Low overload (VT) hp

150 hp

Input voltage range

380 - 500 V

Input frequency range

50 - 60 Hz

Output frequency range

0 - 400 Hz

Max overload

110% for 1 minute

Recommended fuse size

250

Communications onboard

EtherNet/IP, Modbus TCP, RS-485: Modbus RTU, BACnet
MS/TP

Motor control modes

Frequency, Speed, Open-loop speed, Open-loop torque

Motor type

Inductio, PM (IPM & SPM)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)