



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHR7N7NS 20A 125V 2P GFI Metered PWR Panel

Eaton Corp

Catalog Number	CHR7N7NS
Manufacturer	Eaton Corp
Description	Metered-Ringless Power Panel, 20 A, 125 V, 25.4000 CM Overall Length, 20.3200 CM Overall Width, 78.7400 CM Overall Height, Surface Mount, 24 LB/Ea
Weight per unit	24.0 (lbs/each)
Product Category	Metered Power Outlet Panels

Features

dimensions	78.7400centimetreX25.4000centimetreX20.3200centimetre
Number of Circuits	4 in

Descriptions

Description	20A 125V 2P GFI METERED PWR PANEL
-------------	-----------------------------------

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114203293
sub brand	None Mount
UPC	782114203293

Taxonomies, Classifications, and Categories

Category Description	TEMP. POWER PANELS & ACCESSORIES
igcc	4439
Type	Pedestal mount metered
unspsc code	39121309

Packaging

Carton	1
Weight Per each	24

Uses, Certifications, and Standards

Mounting	Surface mounting
standard	UL 231;UL Listed file E163588



Powering Business Worldwide

pe.eaton.com

Eaton pedestal mount metered

CHR7N7NS

UPC:782114203293

Dimensions:

- **Height:** 8 IN
- **Length:** 31 IN
- **Width:** 10 IN

Weight:24 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Metered-ringless
- **Circuit Breaker Position 1:** Ground fault
- **Circuit Breaker Position 2:** Non-ground fault
- **Circuit Breaker Position 3:** None
- **Feed Type:** Top
- **Mounting:** Surface
- **Number Of Circuits:** 4
- **Receptacle Center:** NEMA 5-20R2GFI

Supporting documents:

- [Dimensional Drawing - POWER OUTLET, SURFACE MOUNT, METERED](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CHR7N7NS](#)

Certifications:

- UL Listed file E163588
- UL 231

Product compliance: No Data



