



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8620 E 34th St N  
67226-0000, KS Wichita  
Phone: 316-247-8220  
Fax: 000-000-0000



## DH362FDK 60A/3P HD Fusible Safety Switch 600V Nema 12

Eaton Corp

Catalog Number	DH362FDK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Receptacle Safety Switch, 60 A, Nema 12/3R, Painted Galvanized Steel, Class H, Fusible Without Neutral, Three-Pole, Three-Wire, 600 V, Max HP: 20, 25/ 30, 50 HP (1/3PH @480, 600 V), #14-#2 Cu/Al
Weight per unit	19.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	60
Material	Galvanized Steel
media	Yes
Poles	Three-pole
Voltage Rating	600 V

### Dimensions and Weight

Depth	20
Height	8.5
Width	9.5

### Descriptions

Description	60A/3P HD FUSIBLE SAFETY SWITCH 600V NEMA 12
extra long description	ETN DH362FDK 60A/3P HD Fusible Sfty
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty receptacle safety switch, 60 A, NEMA 12/3R, Painted galvanized steel, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 20, 25/ 30, 50 hp (1/3PH @480, 600 V), #14-#2 Cu/Al
Product Type	60A/3P HD Fusible Sfty SW 600V N12

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113206141
Manufacturers Part Number	DH362FDK
UPC	782113206141

### Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8620 E 34th St N  
67226-0000, KS Wichita  
Phone: 316-247-8220  
Fax: 000-000-0000

## Packaging

Carton	1
Weight Per each	19

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	12:3R
standard	UL Listed