



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH362NRK 60A 600V 4SN SW Nema3r *Eaton Corp*

| | |
|------------------|--|
| Catalog Number | DH362NRK |
| Manufacturer | Eaton Corp |
| Description | Safety Switch, 60 A, 480 to 600 V Ac;250 V DC, 3 Poles, 4 Wires, Class H Fuse, Painted Galvanized Steel (Enclosure) Material, 8.13 In Overall Length, 10 In Overall Width, 15.88 In Overall Height, Fusible, 20 LB |
| Weight per unit | 20.0 (lbs/each) |
| Product Category | Fusible Heavy Duty Safety Swit |

Features

| | |
|----------------------|--|
| amperage rating | 60 WTT |
| dimensions | 41.9100centimetreX23.4950centimetreX20.9550centimetre |
| fuse class provision | Class H fuses |
| fuse configuration | Fusible with neutral |
| max hp rating | 20 at 480 Vac TD 1 Ph, 25 at 600 Vac TD 1 Ph, 30 at 480 Vac TD 3 Ph, 50 at 600 Vac TD 3 Ph |
| Poles | 3 Im |
| product category | Heavy Duty, Fusible with neutral |

Material, Color, and Finish

| | |
|--------------------|--------------------------|
| Enclosure Material | Painted galvanized steel |
|--------------------|--------------------------|

Descriptions

| | |
|-------------|------------------------|
| Description | 60A 600V 4SN SW NEMA3R |
|-------------|------------------------|

Manufacturer Information

| | |
|-----------|---------------------|
| Brand | EATON CUTLER-HAMMER |
| GTIN | 00782113206059 |
| sub brand | None IN |
| UPC | 782113206059 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------|
| Category Description | DISCONNECTS |
| igcc | 5166 |
| Type | Single-Throw |
| unspsc code | 39122205 |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 20 |

Uses, Certifications, and Standards

| | |
|-----------|-----------|
| Enclosure | NEMA 3R |
| standard | UL Listed |

EATON | Cutler-Hammer

Heavy-Duty Safety Switch with Bussmann® CUBEFuse™ Fuse Clips

Product Focus



Introduction

Utilizing Bussmann CUBEFuse fuse clips and larger line side shielding, the new Heavy-Duty Safety Switch with CUBEFuse provisions provides customers an enhanced finger-safe switch with virtually no exposed live parts — even with the door open. This increased protection helps to address a concern that is on many users' minds — arc flash safety. By minimizing the potential of accidental contact with live components, this new offering protects personnel from possible harm.

Unlike standard fuses that have exposed ferrules, Bussmann's CUBEFuse is a stab-in fuse with connection points on the back of the fuse. This design eliminates the possibility of contacting an energized part of the fuse when the switch door is opened, and the switch is in the ON position. Additionally, the new, larger line shield

provides better protection against accidental contact with the safety switch line terminals — that may remain energized even when the switch handle is in the OFF position.

The CUBEFuse is a dual-element, time-delay fuse with Class J Current-Limiting performance. CUBEFuses are 600-volt class with a minimum time delay of 10 seconds at 500% of current. This longer delay reduces the number of nuisance blown fuses caused by temporary overloads and transient surges, making the CUBEFuse ideal for motor circuits.

CUBEFuses are available from 1 – 100 amperes and have standard, built-in blown-fuse indicators to allow operators to ascertain quickly which fuse has opened. This feature provides real value, particularly when employed in a safety switch with viewing window.

The Heavy-Duty Safety Switch with CUBEFuse is available in 30, 60 and 100 ampere ratings and in five different enclosures including NEMA® 1, 3R, 12, 4X (stainless) and 4X Halyester™.

The NEMA 12 and 4X (stainless) are available with a window option, providing increased visibility to the blown fuse indicator, and the NEMA 4X Halyester is available with the clear cover option providing the same functionality. Switches are rated 200 kAIC at 600 Vac throughout the entire product range.

Standard Features


- Extended line terminal shield.
- "Finger-safe" 30-, 60- or 100-ampere Bussmann CUBEFuse fuse base.
- 200 kAIC interrupting rating, at 600 Vac.
- Visible double break quick-make, quick-break rotary blade K-Switch mechanism.
- Triple padlocking capability.
- Mechanically interlocked door.

Optional Features

- Viewing window for visible blades and blown fuse indication.
- NEMA 1, 3R, 12, 4X (stainless) and 4X Halyester enclosures.
- EnviroLine stainless steel mechanism.
- Factory-installed Flex Center options.

Standards and Ratings

- UL® 98 standard for enclosed deadfront switches.
- UL 50 standard for enclosures for electrical equipment.
- 600 Vac maximum.
- 30 – 100 amperes; 3-, 4- and 6-poles.





NEMA 1 CUBEFuse Safety Switch



Enhanced Line Shield




Halyester CUBEFuse Safety Switch with Clear Cover



Enhanced Line Shield and Interlock Defeater

CUBEFUSE SWITCH CATALOG NUMBERING SYSTEM



Eaton Electrical Inc.
1000 Cherrington Parkway
Moon Township, PA 15108
United States
tel: 1-800-525-2000
www.EatonElectrical.com

Bussmann is a registered trademark of Cooper Industries, Inc. NEMA is the registered trademark and service mark of the National Electrical Manufacturers Association. UL is a registered trademark of Underwriters Laboratories Inc. Cutler-Hammer is a federally registered trademark of Eaton Corporation.



© 2007 Eaton Corporation
All Rights Reserved
Printed in USA
Publication No. PA00801005E / Z5299
January 2007