

# **FEATURES & SPECIFICATIONS**

## INTENDED USE

For use with housings LCP, LC6, L7X, L7XP, L7XPR and L7XR.

### CONSTRUCTION

Aluminum white reflector.

Polyester powder coat paint.

White finish has integral flange.

### INSTALLATION

Socket to trim interface.

Retaining clips riveted to top of reflector hold trim inside housing.

#### LISTINGS

 $\label{thm:condition} \textbf{UL Listed to US and Canadian safety standards.}$ 


Wet location listed.

### WARRANTY

1-year limited warranty. Complete warranty terms located at <a href="https://www.acuitybrands.com/CustomerResources/Terms">www.acuitybrands.com/CustomerResources/Terms</a> and conditions.aspx

Actual performance may differ as a result of end-user environment and application.

Note: Specifications subject to change without notice.



6" Finishing Trim



**CL1/2** 

POLYCARBONATE LENS

Narrow Flange





Flush opal lens

Flush prismatic lens


Specifications

Height: 4 (10.2)

Lamp opening: 5-5/8 (14.3)

Diameter: 7-5/8 (19.4)

All dimensions are inches (centimeters) unless otherwise indicated.



Example: CLD1

ORDERING INFORMATION `

For shortest lead times, configure product using **bolded options**.

Series		0ptio	Options			
CLD1	Drop opal lens	PF	Integral white plastic flange <sup>1</sup>			
CLF1	Flush opal lens					
CLF2	Flush prismatic lens					

Housing Compatibility: Housing and trim ordered separately.						
Application	Source	Maximum wattage	Housing			
16	Incandescent	40 A19	LCP, LC6, L7X, L7XR			
IC	Fluorescent	13DTT	L7XF			

#### Notes

DOWNLIGHTING CL1-2

<sup>1</sup> Flush lens (CLF1, CLF2) with plastic flange option is not compatible with CFL housings.

