ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1205 N Eliseo Felix Jr. Way Suite A101
85323-0000, AZ Avondale
Phone: 623-259-1366
Fax: 623-259-1367



CPR29 3-1/2" Rigid Coupling Threadless

Crouse-Hinds

Catalog Number	CPR29
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series CPR Compression Coupling, Rigid/Imc, Malleable Iron, Compression Type, 3-1/2"
Weight per unit	4.4 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

dimensions	4.7500 IN X 4.2500 IN X 4.2500 IN
Material	Malleable Iron

Descriptions

Description	3-1/2" RIGID COUPLING THREADLESS
extra long description	CRH CPR29 3 1/2 RGD CMP CPL
Features	Crouse-Hinds series rigid/IMC connectors, couplings and combination couplings are used to join used to join rigid/IMC conduit to a box or enclosure, or to couple two ends of conduit together. Our rigid/IMC connectors and couplings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in a variety of materials to suit customer preferences, including malleable iron, steel, zinc die cast, aluminum, stainless steel and hot dip galvanized mallea
Long Description	Eaton Crouse-Hinds series CPR compression coupling, Rigid/IMC, Malleable iron, Compression type, 3-1/2"
Product Type	3 1/2 RGD CMP CPL
Special Features	Concrete Tight, Weight 380 Lb per 100

Manufacturer Information

Brand	Eaton
GTIN	00784564122292
Manufacturers Part Number	CPR29
UPC	784564122292

Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Compression coupling

Packaging

Carton	1
Weight Per each	4.4

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1205 N Eliseo Felix Jr. Way Suite A101
85323-0000, AZ Avondale
Phone: 623-259-1366
Fax: 623-259-1367

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL 514B, CUL