



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CPR4 1-1/4" Rigid Connector Threadless

*Crouse-Hinds*

Catalog Number	CPR4
Manufacturer	Crouse-Hinds
Description	Connector, 1-1/4 In Trade Size, CPR Model, Straight, Non-Insulated, 64 LB/100
Weight per unit	0.2200 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

Material	MALLEABLE IRON
----------	----------------

### Dimensions and Weight

Size	1-1/4 In
------	----------

### Descriptions

Construction	Concrete Tight
Description	1-1/4" RIGID CONNECTOR THREADLESS

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00784564122049
UPC	784564122049

### Taxonomies, Classifications, and Categories

Category Description	MYER'S HUB, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTORS
Type	Compression Connector, Non-Insulated

### Packaging

Carton	10
Weight Per each	0.22

### Uses, Certifications, and Standards

standard	UL 514B, CUL
----------	--------------

# Rigid/Intermediate Grade Conduit Fittings

## Compression Fittings – Type CPR

### TYPE CPR COMPRESSION FITTINGS

#### Applications:

Use type CPR compression fittings for:

- Both IMC and metallic rigid conduit
- New work in poured concrete
- Maintenance, repairs and alterations
- Connections at panels and boxes
- New, altered or damaged stub-ups
- Applicable locations where field threading is impractical or undesirable

#### Features:


- UL Listed for use with IMC as well as metallic rigid conduit
- Unequaled versatility for the installer
- Unique gland ring design tightens up in fewer turns; provides outstanding pull-out strength; saves time and adds confidence
- Advanced, thoughtful design and premium materials team up for an installation you can be proud of
- Concrete tight
- Threadless

#### Certifications and Compliances:

- UL/cUL Listed
- UL514B Fittings for Conduit and Outlet Boxes

#### Standard Materials:

- Bodies – malleable iron
- Compression nuts – iron
- Compression rings – zinc plated steel
- Locknuts – zinc plated steel
- Insuliners – nylon



#### Straight Connectors – Insulated


UL File No. E-19189



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
CPR11	1/2"	50	19
CPR12	3/4"	25	23
CPR13	1"	10	42
CPR14	1 1/4"	10	64
CPR15	1 1/2"	5	87
CPR16	2"	5	113
CPR17	2 1/2"	2	130
CPR18	3"	1	220
CPR19	3 1/2"	1	280
CPR20	4"	1	320

#### Straight Connectors – Non-insulated


UL File No. E-19189



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
CPR1	1/2"	50	19
CPR2	3/4"	25	23
CPR3	1"	10	42
CPR4	1 1/4"	10	64
CPR5	1 1/2"	5	87
CPR6	2"	5	113
CPR7	2 1/2"	2	130
CPR8	3"	1	220
CPR9	3 1/2"	1	280
CPR10	4"	1	320

#### Couplings

UL File No. E-19189



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
CPR21	1/2"	25	26
CPR22	3/4"	20	38
CPR23	1"	10	59
CPR24	1 1/4"	5	85
CPR25	1 1/2"	5	124
CPR26	2"	2	162
CPR27	2 1/2"	2	220
CPR28	3"	1	320
CPR29	3 1/2"	1	380
CPR30	4"	1	440