

DURAWALL 50 G2

50W LED WALL PACK



250W MH Replacement

| | |
|-------------------|---------------------------------|
| Lumens | 6,250 |
| CCT | 5000K |
| Beam Angle | 120° |
| Operating Voltage | 100-277 VAC |
| Power Consumption | 50W |
| CRI | > 70 |
| Lifespan | > 50,000 Hours |
| IP Grade | IP 65 |
| Body Construction | Die-Cast Aluminum w/ Glass Lens |
| Body Dimensions | 14.3" x 9.4" x 7.6" |
| Weight | 7.6 lbs |

ORDER CODE: DW50-G2-BRZ-5K

Quick Disconnect Wiring: Wiring for the housing and lens are easily connected for effortless and quick installation.

Built-In Bubble Level: For quick and easy leveling and installation.