



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CR15LA Commercial Recp 15A 125V La

Pass & Seymour/Legrand

Catalog Number	CR15LA
Manufacturer	Pass & Seymour/Legrand
Description	Commercial Spec Grade Duplex Receptacle, Side Wire 15A 125V
Weight per unit	0.1956 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Side wire
Dielectric Strength	Withstands 1500V minimum
indoor/outdoor	Indoor
Material	Nylon
Mounting Type	Box
Number of Wires	3
Outlet Type	STRAIGHT BLADE
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Dimensions and Weight

Height	3.281
Width	.780

Descriptions

Description	COMMERCIAL RECP 15A 125V LA
extra long description	P&S CR15LA COMMERCIAL RECEPTACLE 15
Features	Single Piece Plated Steel Mounting Strap, Impact Resistant
Long Description	Commercial Spec Grade Duplex Receptacle, Side Wire 15A 125V
Product Type	Commercial Receptacle 15A/125V La
Special Features	Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body. Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for positive conductor containment. Tri-drive termina



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007608038
Manufacturers Part Number	CR15-LA
UPC	785007608038

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.1956

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-15R
Operating Temperature	-40°-60°C
standard	CULUS, UL498, CSA C22.2 No. 42