



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DZS200BP Multivolt 365 Day Astro Supercap 2 CH. 20A SPDT W/ *Nsi Industries*

Catalog Number	DZS200BP
Manufacturer	Nsi Industries
Description	365 Day Astro Digital Timer 2CH
Weight per unit	2.2 (lbs/each)
Product Category	Electronic Time Switches

Features

action	SPDT
Base	Screw
Contact Rating	120-208-240-277
Phase	Single Phase
Poles	1
Timing Range	365 Day-7 Day Advanced

Dimensions and Weight

Size	L=5.000 - H=9.125 - W=4.500
------	-----------------------------

Descriptions

Description	MULTIVOLT 365 DAY ASTRO SUPERCAP 2 CH. 20A SPDT W/
extra long description	TORK DZS200BP 365 Day Astro Digital
Features	Tork 365/7 Day Advanced 2 Channel SPDT Astronomic Time Switch APPLICATIONS: HVAC Equipment Horns and Bells Interior Lighting Electric Motors Outdoor Lighting and Signs FEATURES: TIMING ACCURACY: Line Frequency INPUT VOLTAGE: 120/208-240/277 50/60Hz DRY CONTACTS: SPDT NO. OF CHANNELS: 2 Channel TERMINAL RANGE: #14-#16AWG for Line Input #12-#16AWG Load Outputs OPERATING TEMPERATURE: -40 degrees to +158 degrees F (-40 degrees to 70 degrees C) POWER CONSUMPTION: 5VA Max SCHEDULING: 99 ON/OFF set points allow i
Long Description	365 Day Astro Digital Timer 2CH
Product Type	365 Day Astro Digital Timer 2CH
Special Features	99 On-Off Set Points - Astronomic Time Switch With Holiday Schedule And Manual Override

Manufacturer Information

Brand	NSi
GTIN	00786261821836
Manufacturers Part Number	DZS200BP
UPC	786261821836



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	1PH MANUAL STARTERS
Type	365 Day-7 Day Advanced

Packaging

Carton	1
Weight Per each	2.2

Uses, Certifications, and Standards

Application	NSI
Enclosure	NEMA 3R Noryl Indoor-Outdoor
environmental conditions	-40 to + 158 F
Frequency Rating	50-60 Hz
Mounting	Screw Mount
Operating Temperature	-40 to + 158 F
standard	UL917