



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CS120GRY 20A 120/277VAC S Wire Comm SP SW Gy *Pass & Seymour/Legrand*

Catalog Number	CS120GRY
Manufacturer	Pass & Seymour/Legrand
Description	Commercial 1-Pole Switch, Side-Wire, 20A 120/277V.
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	Single pole
actuator	Toggle
amperage rating	20
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Fluorescent, Xenon, CFL, Incandescent, Universal, Halogen, LED
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	20A 120/277VAC S WIRE COMM SP SW GY
extra long description	P&S CS20AC1GRY 20A 120/277VAC S WIR
Features	Single Piece Plated Steel Mounting Strap
Long Description	Commercial 1-Pole Switch, Side-Wire, 20A 120/277V.
Product Type	20A 120/277VAC S Wire Comm SP SW Gry
Special Features	Side wire, locking support, heavy duty toggle



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007126570
Manufacturers Part Number	CS20AC1GRY
UPC	785007126570

## Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	10
Package	50
Weight Per each	0.15

## Uses, Certifications, and Standards

Application	Commercial
Enclosure	Nylon
Mounting standard	WALL CULUS, UL 498/20, FEDSPEC