

Eaton E50KL25

Catalog Number: E50KL25

Eaton E50 NEMA heavy duty plug-in limit switch, Lever for Side Rotary Switches, Lever: Stainless Steel, Roller: Powdered Metal - Super Oilite enclosure



General specifications

Product Name

Eaton E50 NEMA heavy duty plug-in limit switch operator

Catalog Number

UPC
782113308944

Product Length/Depth

0.75 in

Product Height

2.3 in

Product Width

1.24 in

Product Weight

0.06 lb

Warranty

1 year

Compliances

RoHS Compliant

Certifications

UL Listed
CSA Certified
CE

Catalog Notes

Lever length is from the operating shaft axis to the roller axis

Type

Mechanical Limit Switches

Enclosure material

Roller: powdered metal-Super Oilite

Lever: stainless steel

Switch type

Lever for side rotary switches

Operating temperature - max

201 °F

Operating temperature - min

-40 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67, IP69K

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50KL25](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)