



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1774 Buildtek Court
88005-0000, NM Las Cruces
Phone: 575-652-6525
Fax: 000-000-0000



ECN05A1AAAR63B Non-Combo Nema 1 FVNR SZ 00 120V Coil

Eaton Corp

Catalog Number	ECN05A1AAAR63B
Manufacturer	Eaton Corp
Description	Eaton Freedom Nema Motor Control Starter, 110V/50 HZ-120V/60 HZ, Nema 1, Non-Combination Non-Reversing Starter, Nema Size 00, 1-5A Solid-State Relay Without Ground Fault
Weight per unit	11.6 (lbs/each)
Product Category	Nema Non-Combination Starters

Features

Coil Voltage	110V/50 Hz-120V/60 Hz
--------------	-----------------------

Dimensions and Weight

Depth	14.9
Height	8.5
Size	NEMA size 00
Width	10.1

Descriptions

Description	NON-COMBO NEMA 1 FVNR SZ 00 120V COIL
extra long description	ETN ECN05A1AAA-R63/B NON-COMBO NEMA
Features	Eaton's Freedom starters and contactors feature a compact, space-saving design, using state-of-the-art technology and the latest in high strength, impact and temperature resistant insulating materials. In addition to the bimetallic overload, Eaton also offers a series of electronic overload relay (C440) available as a standalone unit and assembled with Freedom contactor.
Long Description	Eaton Freedom NEMA motor control starter, 110V/50 Hz-120V/60 Hz, NEMA 1, Non-combination non-reversing starter, NEMA size 00, 1-5A solid-state relay without ground fault
Product Type	Non-Combo Nema 1 FVNR SZ 00 120V Coil

Manufacturer Information

Brand	Eaton
GTIN	00786685450773
Manufacturers Part Number	ECN05A1AAA-R63/B
UPC	786685450773

Taxonomies, Classifications, and Categories

Category Description	ENCLOSED
----------------------	----------

Packaging

Carton	1
Weight Per each	11.6



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1774 Buildtek Court
88005-0000, NM Las Cruces
Phone: 575-652-6525
Fax: 000-000-0000

Uses, Certifications, and Standards

Application	Unknown - Unknown: Undefined
standard	UL Listed file E1491,Contact Manufacturer