



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

425 East Germann Road Suite 101  
85297-0000, AZ Gilbert  
Phone: 602-325-9757  
Fax: 602-325-9758



## ED3125 Ed 65KA @ 240 V 3 Pole 125AS Load Terms *Eaton Corp*

Catalog Number	ED3125
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, Ed, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Three-Pole, 125 A, 240 Vac, 125 VDC, 65 Kaic At 240 Vac, 50/60 HZ
Weight per unit	4.3 (lbs/each)
Product Category	3 Pole

### Features

Current Rating	125 A
dimensions	3.3800 IN X 4.1300 IN X 6.0000 IN
frame	F
Poles	3
Voltage Rating	240 Vac, 125 Vdc

### Descriptions

Description	ED 65KA @ 240 V 3 POLE 125AS LOAD TERMS
extra long description	ETN ED3125 ED 65kA @240 V, 3P 125 A
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, ED, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 125 A, 240 Vac, 125 Vdc, 65 kAIC at 240 Vac, 50/60 Hz
Product Type	Ed 65KA @240 V, 3P 125 As, Load Terminal

### Manufacturer Information

Brand	Eaton
GTIN	00786679455326
Manufacturers Part Number	ED3125
UPC	786679455326

### Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

425 East Germann Road Suite 101  
85297-0000, AZ Gilbert  
Phone: 602-325-9757  
Fax: 602-325-9758

## Packaging

Carton	1
Weight Per each	4.3

## Uses, Certifications, and Standards

Application	Other
standard	UL Listed