



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St
70123-0000, LA Harahan
Phone: 504-264-9995
Fax: 504-264-5996



CSPB3624 33.72X21.75 Swngout PNL

Hoffman Enclosures, Inc.

Catalog Number	CSPB3624
Manufacturer	Hoffman Enclosures, Inc.
Description	Concept Swing-Out Panel, Fits 36.00X24.00, White, Steel
Weight per unit	23.5 (lbs/each)
Product Category	Enclosure General Accessories

Features

Material	Mild Steel;Steel
----------	------------------

Material, Color, and Finish

Color	White
Finish	Powder Coated

Dimensions and Weight

Size	fits 36.00x24.00 in
------	---------------------

Descriptions

Description	33.72X21.75 SWNGOUT PNL
extra long description	NVENT HOF CSPB3624 Panel, Swing out
Features	Panels swing clear from the front of the enclosure to provide access to mounted internal equipment. For CSPB panels, maximum swing is 94 degrees. For CSP panels, maximum panel swing is 106 degrees. Distance from panel surface to door when in the latched position is 1.71 in. (43 mm) for solid doors and 1.45 in. (37 mm) for window doors. Kits include panel, brackets and hardware to mount to the front flange. Swing-out panels also can be mounted on front-to-back adjustable rails. CSPB panels require adapter C
Long Description	Concept Swing-Out Panel, fits 36.00x24.00, White, Steel
Product Type	Panel, Swing Out, 36X24
Short Description	Panel, Swing out, 36x24

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510165048
Manufacturers Part Number	CSPB3624
UPC	783510165048

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Industrial Panels and Panel Accessories



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St
70123-0000, LA Harahan
Phone: 504-264-9995
Fax: 504-264-5996

Packaging

Carton	1
Weight Per each	23.5

Uses, Certifications, and Standards

Application	Arc Flash Safety;Controls and Drives;Power Distribution
-------------	---