



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive  
30336-0000, GA Atlanta  
Phone: 470-237-5352  
Fax: 470-237-5353



## EHD2040 Type Ehd BRKR 2P 40A 480VAC Max 14kaic *Eaton Corp*

Catalog Number	EHD2040
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, Ehd, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 40 A, Load Side, 50/60 HZ
Weight per unit	3.0 (lbs/each)
Product Category	2 Pole

### Features

Current Rating	40 A
dimensions	3.3800 IN X 2.7500 IN X 6.0000 IN
frame	F
media	Yes
Poles	Two-pole

### Descriptions

Description	TYPE EHD BRKR 2P 40A 480VAC MAX 14KAIC
extra long description	ETN EHD2040 TYPE EHD BRK 2P 40A 480
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, EHD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 40 A, Load side, 50/60 Hz
Product Type	Type Ehd BRK 2P 40A 480VAC Max 14kaic

### Manufacturer Information

Brand	Eaton
GTIN	00786679317464
Manufacturers Part Number	EHD2040
UPC	786679317464

### Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive  
30336-0000, GA Atlanta  
Phone: 470-237-5352  
Fax: 470-237-5353

## Packaging

Carton	1
Weight Per each	3

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
standard	UL Listed