

Photocontrol - NightFox™ Stem Mount Electronic Photocontrol, 480 V

Item EK4135S



PRODUCT DESCRIPTION

NightFoxTM electronic photocontrols permanently install on outdoor electrical boxes or outdoor lighting fixtures. Ideal for LED fixtures with long-life expectations. ½"-14 NPSM threaded stem fits standard outlet boxes and wall packs with a minimum installation hole size of 7/8" diameter. Come with 9" wire leads.

FEATURES

- ► Non-drift silicon light sensor with IR filter
- ► DC relay with zero-crossing circuitry for extended life
- ► Conformal coated PCB
- ► 15-year design life
- ► Exceeds 10,000 ON/OFF switching cycles
- ► Fail ON mode
- ▶ Ideal for single or multi fixture HID and LED installations
- ▶ 220J MOV surge protection element
- ► 1/2"-14 NPSM threaded stem fits standard outlet boxes and wall packs for a minimum installation hole size of 7/8 inch diameter
- ► #18 AWG wire leads

APPLICATIONS

► Outdoor Lighting Control

TECHNICAL DATA

OA20

General	
Model Number	EK4135S
Description	NightFox™ Stem Mount Electronic Photocontrol, 480 V
UPC Code	078275152403
Brand	Intermatic
Country of Origin (Intermatic)	MEXICO
Warranty Period	8-Year limited
Usage Environments	Outdoor
Photocontrol Type	Electronic
Expected Lifetime (Years)	15
Expected Lifetime (Operations)	10000
Application Compatibilities	LED; Incandescent; HID
Photocontrol Style	Stem Mount
Photocontrol Sensor Location	Side

Control Specifications	
Sensor Time Delay	Instant ON; 2 sec to 5 sec OFF
Photocell Type	Silicon Diode
Photo Control Switch Type	Relay
Fail Mode	ON
Activation On	1.5 fc
Activation Off	4.5 fc

Dimensions



Product Height (in)	2 1/4
Product Height (mm)	57.2
Product Width (in)	1 5/16
Product Width (mm)	33.3
Product Depth (in)	1 1/4
Product Depth (mm)	31.8
Wire Lead Length (in)	9
Wire Lead Length (mm)	228.6
Wire Size Max	#18 AWG

Material Specifications	
Cover Color	Gray
Housing Material	Polycarbonate

Load Ratings	
Tungsten Range(s)	1000 W
Ballast Fluorescent Ranges	1800 VA
Electronic Ballast Load Ratings Ranges	0.35 A (Tested with 150 W 480 V LED driver with 120 Apk /100µs In-rush current)

Electrical Specifications		
Wiring Option	Wire leads	
Input Voltage Range(s)	480 VAC, 50/60 Hz	
Surge Protection Technology	220 J MOV. 5.000 A Surge	


Packaging	
Shipping Weight (lbs)	0.215
Unit Carton Dimensions (H x W x D) in	4.875 x 3 x 1.75 in


Environmental Specifications	
Temperature (operation)	-40°C70°C


Standards and Certifications	
Other Certifications and Compatibilities	Title 20; Ansi C136.24
California Proposition 65	Nickel; DEHP
RoHS Certification	No



DRAWINGS AND DIAGRAMS









ACCESSORIES



22LG0120 Light Guard Accessory for EK4000 Series Electronic Fix Mount Photocontrols



LGLBL
Lens Sticker Accessory for EK4000 & K4000 Series Photocontrols