



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EL39 1" 90D Female-Female Cond Elbow *Crouse-Hinds*

Catalog Number	EL39
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series EL Elbow, Female, Feraloy Iron Alloy or Ductile Iron, 90°, 1"
Weight per unit	0.3800 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Female Threaded
dimensions	2.8800 IN X 1.7500 IN X 2.8800 IN

### Descriptions

Description	1" 90D FEMALE-FEMALE COND ELBOW
extra long description	CRS-H EL39 1 NPT IRON 90 DEG FEMALE
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit
Long Description	Eaton Crouse-Hinds series EL elbow, Female, Feraloy iron alloy or ductile iron, 90°, 1"
Product Type	1 NPT Iron 90 Deg Female Div 1 Elbow

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274307404
Manufacturers Part Number	EL39
UPC	782274307404

### Taxonomies, Classifications, and Categories

Category Description	RIGID ELBOWS
Type	ELBOW

### Packaging

Carton	1
Package	10
Weight Per each	0.38



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group A B C D, Class II Div 1 Group E F G, Class II
	Div 2 Group F G, Class III
standard	UL 886, CSA C22.2