



On-Q
42-inch Enclosure with Hinged Door
Part No. EN4250



Perfect for larger installations, this 42" enclosure features universal On-Q style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more s

Features & Benefits

42-in Enclosure with Hinged Door	Drywall depth indicators
Flush and surface installation	Mounting tabs provide correct flush-mount position for standard installations
Patented mounting system offers versatile module mounting options	Literature pouch included for dealer information
Includes self-adhesive cable identification table	Cover included
Made in the USA	

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023180	Country Of Origin	United States
Material	Steel	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	42.0 in	Enclosure Size	42 in

Listing Agencies / 3rd Party Agencies

CSA Listed

Yes

cULus Listed

Yes

Additional Information

RoHS Compliant

Yes

Technical Information

Thickness

0.1 in

Cable Entry

(6) rear knockouts

Frame

Cold Rolled Steel



On-Q
42-inch Enclosure with Hinged Door
Part No. EN4250



Perfect for larger installations, this 42" enclosure features universal On-Q style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more s

Features & Benefits

42-in Enclosure with Hinged Door	Drywall depth indicators
Flush and surface installation	Mounting tabs provide correct flush-mount position for standard installations
Patented mounting system offers versatile module mounting options	Literature pouch included for dealer information
Includes self-adhesive cable identification table	Cover included
Made in the USA	

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023180	Country Of Origin	United States
Material	Steel	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	42.0 in	Enclosure Size	42 in

Listing Agencies / 3rd Party Agencies

CSA Listed

Yes

cULus Listed

Yes

Additional Information

RoHS Compliant

Yes

Technical Information

Thickness

0.1 in

Cable Entry

(6) rear knockouts

Frame

Cold Rolled Steel
