



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



D15CR22AB Freedom Series Relay 2NO/2NC 120vac

Eaton Corp

Catalog Number	D15CR22AB
Manufacturer	Eaton Corp
Description	Eaton Nema Machine Tool Relay, D15 Series, Freedom, 600V Multi-Pole Relay, Four-Pole, 110/120V Coil Voltage, 50/60 HZ, 2NO-2NC Contact Configuration, 60A Make, 6.0A Break Contact Rating, 10A Rated Operational Current
Weight per unit	2.2 (lbs/each)
Product Category	Nema Control Relays & Accy.

Features

Contact Configuration	2 NO-2 NC
Contact Rating	60 A make, 6 A break
dimensions	3.8000 IN X 4.0000 IN X 2.6000 IN
Poles	Four-pole

Descriptions

Description	FREEDOM SERIES RELAY 2NO/2NC 120VAC
extra long description	ETN D15CR22AB FREEDOM SERIES RELAY
Features	NEMA machine tool relays include the Freedom 600 V multi-pole (D15), fixed contact industrial control (BF, BFD), convertible contact industrial control (AR, ARD) and type M, multi-pole with convertible contacts (D26). These relays can be ordered as complete devices in any pole combination up to a maximum of 12NO or 8NC and 4NO poles. They are also designed for use on machines, process lines, conveyors and similar automatic and semiautomatic equipment.
Long Description	Eaton NEMA machine tool relay, D15 Series, Freedom, 600V Multi-pole Relay, Four-pole, 110/120V coil voltage, 50/60 Hz, 2NO-2NC contact configuration, 60A make, 6.0A break contact rating, 10A rated operational current
Product Type	Freedom Series Relay 2NO/2NC 120vac

Manufacturer Information

Brand	Eaton
GTIN	00782113807157
Manufacturers Part Number	D15CR22AB
UPC	782113807157

Taxonomies, Classifications, and Categories

Type	Machine tool relay
------	--------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	2.2

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Frequency Rating	50-60 Hz
standard	UL Listed, CSA Certified