

Key Features & Benefits:

- Up to 125 Lumens per Watt
- Glass Construction with Shatterproof Coating
- > 220° Beam Spread
- Double Ended or Single Ended Wiring
- Integral Driver (Isolated)



Project:

Date:

Catalog #:

Notes:




Technical Specifications:


Power: 15 Watts
 Input Voltage: 120-277 VAC
 Lumen Output: Up to 1,941 Lumens
 Efficacy (lm/W): Up to 125 Lumens per Watt
 Kelvin: 3000K, 3500K, 4000K, 5000K
 Color Rendering Index (CRI): >80
 Material: Glass with PET Coating
 Power Factor: >0.9
 Rated Life (hrs): 50,000 Hours
 Base Type: G13
 Operating Temperature: -4°F ~ 113°F (-20°C ~ 45°C)
 Tube Dimensions (ØxL): 1" x 47.75"
 Tube Weight (lbs): 0.4 Pounds

GLV Wire Diagrams (Type B):

Before Upgrade:



After Upgrade:



ITEM#	WATTS	LUMEN OUTPUT	EFFICACY (lm/W)	KELVIN	DLC QPL CODE
ESL-T8-GLV-15W-F130	15W	1,854	121	3000K	PS2Y58JZ
ESL-T8-GLV-15W-F135*	15W	1,876	122	3500K	PZ7J1UP4
ESL-T8-GLV-15W-F140*	15W	1,898	123	4000K	PSHW4VAM
ESL-T8-GLV-15W-F150*	15W	1,941	125	5000K	PSTK7OS1

*QUICK SHIP ITEMS

Ordering Guide:

Example Part Number: **ESL-T8-GLV-15W-F135**

ESL	-	T8	-	GLV	-	15W	-	F	-	1	-	
ESL		T8		TYPE		WATTS		LENS		GENERATION		KELVIN
		T8 Tube		Glass Line Voltage (4ft)		15W (15 Watts)		F (Frosted)		1 (1st Generation)		30 (3000 Kelvin) 35 (3500 Kelvin) 40 (4000 Kelvin) 50 (5000 Kelvin)



Key Features & Benefits:

- Up to 125 Lumens per Watt
- Glass Construction with Shatterproof Coating
- > 220° Beam Spread
- Double Ended or Single Ended Wiring
- Integral Driver (Isolated)



Project:

Date:

Catalog #:

Notes:




Technical Specifications:


Power: 15 Watts
 Input Voltage: 120-277 VAC
 Lumen Output: Up to 1,941 Lumens
 Efficacy (lm/W): Up to 125 Lumens per Watt
 Kelvin: 3000K, 3500K, 4000K, 5000K
 Color Rendering Index (CRI): >80
 Material: Glass with PET Coating
 Power Factor: >0.9
 Rated Life (hrs): 50,000 Hours
 Base Type: G13
 Operating Temperature: -4°F ~ 113°F (-20°C ~ 45°C)
 Tube Dimensions (ØxL): 1" x 47.75"
 Tube Weight (lbs): 0.4 Pounds

GLV Wire Diagrams (Type B):

Before Upgrade:



After Upgrade:



ITEM#	WATTS	LUMEN OUTPUT	EFFICACY (lm/W)	KELVIN	DLC QPL CODE
ESL-T8-GLV-15W-F130	15W	1,854	121	3000K	PS2Y58JZ
ESL-T8-GLV-15W-F135*	15W	1,876	122	3500K	PZ7J1UP4
ESL-T8-GLV-15W-F140*	15W	1,898	123	4000K	PSHW4VAM
ESL-T8-GLV-15W-F150*	15W	1,941	125	5000K	PSTK7OS1

*QUICK SHIP ITEMS

Ordering Guide:

Example Part Number: **ESL-T8-GLV-15W-F135**

ESL	-	T8	-	GLV	-	15W	-	F	-	1	-	
ESL		T8		TYPE		WATTS		LENS		GENERATION		KELVIN
		T8 Tube		Glass Line Voltage (4ft)		15W (15 Watts)		F (Frosted)		1 (1st Generation)		30 (3000 Kelvin) 35 (3500 Kelvin) 40 (4000 Kelvin) 50 (5000 Kelvin)

