A

Super B Connectors



- ☑ No Wire Stripping
- ☑ Quick Installation
- ☑ No Clean Up



Dolphin Super B Connectors provide the industry's most reliable connection with their unique design and tine structure. They reduce costs, will not corrode and do not require insulation stripping of most wire gauges before insertion. They also allow for connection testing without stripping wires for faster installations with less clean-up time. These features ensure the continued operation of the security, safety and communications systems in which our connectors are most frequently used.

DESIGN FEATURES

- UL Listed E172979
- Unique Funnel-Entry Design:
 - » Allows Easier Wire Insertion
 - » Eliminates Wire Strand Hang-Up
 - » Positions Wire Perfectly for a Single Crimp
- Accepts 16-24 gauge wires
 - » Larger Opening for multiple wires and heavier wire insulation
- Razor-Sharp Insulation Piercing Teeth
- ISO 9001

RECOMMENDED TOOLS

(See Tools in Section F for pictures.)

- DC-4141 Ratchet Full Cycle Crimping Tool
- DC-500F Hand Tool

DOLPHIN® SEALANT #27B

- Moisture Resistant Barrier
- Non-Curing Sealant
- Will Not Leak Out When Crimped
- Will Not Corrode
- Withstands Temperature Range of -60°F to 475°F

WIRE CAPACITY

4-wires: #24 AWG, #22 AWG (insulated)
3-wires: #20 AWG, #18 AWG (insulated)

#16 AWG (stripped)

ITEM#	DESCRIPTION	QTY/PACK
DC-1000-P	PLAIN (NO SEALANT), WHITE	1000 PIECES PER BOX*
DC-100-P	PLAIN (NO SEALANT), WHITE	100 PIECES PER BAG
DC-1000-S	SEALANT (FILLED), BLUE	1000 PIECES PER BOX*
DC-100-S	SEALANT (FILLED), BLUE	100 PIECES PER BAG

^{*}FREE 15 compartment hanging box with 1000 piece packages!