



EYS41 1-1/4" Fem Cond Seal *Crouse-Hinds*

Catalog Number	EYS41
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Eys Conduit Sealing Fitting, Female, Feraloy Iron Alloy and/or Ductile Iron, Vertical or Horizontal, Group B Rated, 1-1/4"
Weight per unit	2.8 (lbs/each)
Product Category	Sealing Bodies

Features

connection	Female Threaded, Female Threaded
dimensions	2.1900 IN X 2.1900 IN X 5.0600 IN

Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

Descriptions

Description	1-1/4" FEM COND SEAL
extra long description	CRS-H EYS41 1 1/4 NPT FEM CST IRON
Features	Crouse-Hinds series EYS and EZS explosionproof sealing fittings restrict the passage of gases, vapors or flames from one portion of the electrical installation to another, limit explosions to the sealed off enclosure, and limit pre-compression or "pressure piling" in conduit systems. EYS sealing fittings are available for installation in either vertical only or in both horizontal or vertical positions. They are available in a variety of materials, including Feraloy iron alloy and/or ductile iron, copper-
Long Description	Eaton Crouse-Hinds series EYS conduit sealing fitting, Female, Feraloy iron alloy and/or ductile iron, Vertical or horizontal, Group B rated, 1-1/4"
Product Type	1 1/4 NPT Fem CST Iron Ver/Hor Seal FTG
Special Features	Horizontal/Vertical Position

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274379104
Manufacturers Part Number	EYS41
UPC	782274379104

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Conduit sealing fitting



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1821 North Topping Avenue
64120-0000, MO Kansas City
Phone: 913-227-4257
Fax: 816-656-2196

Packaging

Carton	1
Package	2
Weight Per each	2.75

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure standard	Class I Div 1 2 Group B C D, Class II Div 1 2 Group E F G, Class III
	UL 886, CSA C22.2