



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 North Nelson Street
79735-0000, TX Fort Stockton
Phone: 432-336-8730
Fax: 432-336-3279



DH366URK 600A/3P HD NF Safety Switch 600V Nema 3R

Eaton Corp

Catalog Number	DH366URK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Non-Fused Safety Switch, Single-Throw, 600 A, Nema 3R, Painted Galvanized Steel, Non-Fusible, Three-Pole, Three-Wire, 200 At 240 Vac TD 3 PH, 400 At 480 Vac TD 3 PH, 500 At 600 Vac TD 3 PH
Weight per unit	135.0 (lbs/each)
Product Category	Non-Fusible Heavy Duty Safety

Features

amperage rating	600
Material	Galvanized Steel
Poles	3
Voltage Rating	600 V

Dimensions and Weight

Depth	14.07
Height	51.82
Width	25.01

Descriptions

Description	600A/3P HD NF SAFETY SWITCH 600V NEMA 3R
extra long description	ETN DH366URK 600A/3P HD NF Sfty Sw
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 600 A, NEMA 3R, Painted galvanized steel, Non-Fusible, Three-pole, Three-wire, 200 at 240 Vac TD 3 Ph, 400 at 480 Vac TD 3 Ph, 500 at 600 Vac TD 3 Ph
Product Type	600A/3P HD NF Sfty SW 600V N3R

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113207582
Manufacturers Part Number	DH366URK
UPC	782113207582

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Non-Fusible Safety Switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 North Nelson Street
79735-0000, TX Fort Stockton
Phone: 432-336-8730
Fax: 432-336-3279

Packaging

Carton 1

Weight Per each 135

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power
Distribution and Controls

nema rating 3R

standard UL Listed, NEC 230.62 (C) Compliant Barrier