



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH366URK 600A/3P HD NF Safety Switch 600V Nema 3R

Eaton Corp

Catalog Number	DH366URK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Non-Fused Safety Switch, Single-Throw, 600 A, Nema 3R, Painted Galvanized Steel, Non-Fusible, Three-Pole, Three-Wire, 200 At 240 Vac TD 3 PH, 400 At 480 Vac TD 3 PH, 500 At 600 Vac TD 3 PH
Weight per unit	135.0 (lbs/each)
Product Category	Non-Fusible Heavy Duty Safety

Features

amperage rating	600A
dimensions	14.0700 IN X 25.0100 IN X 51.8200 IN
Material	Painted galvanized steel
media	Yes
Poles	Three-pole
Voltage Rating	600 V

Descriptions

Description	600A/3P HD NF SAFETY SWITCH 600V NEMA 3R
extra long description	ETN DH366URK 600A/3P HD NF Sfty Sw
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 600 A, NEMA 3R, Painted galvanized steel, Non-Fusible, Three-pole, Three-wire, 200 at 240 Vac TD 3 Ph, 400 at 480 Vac TD 3 Ph, 500 at 600 Vac TD 3 Ph
Product Type	600A/3P HD NF Sfty SW 600V N3R

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113207582
Manufacturers Part Number	DH366URK
UPC	782113207582

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Non-Fusible Safety Switch

Packaging

Carton	1
Weight Per each	135



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Power

Distribution and Controls

nema rating

Nema 3R

standard

UL Listed, NEC 230.62 (C) Compliant Barrier