



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F13BX841EC0 13W 2 Pin Single Tube Biax GX23 4100K Compact

Ge By Current Lamps

Catalog Number	F13BX841EC0
Manufacturer	Ge By Current Lamps
Description	Compact Fluorescent Lamp, GX23 2-Pin Base, A21 Bulb Shape, 82, 10000 H Average Life, 4100 K, 13 W, 825 LM Brightness (Lumens), Non Dimmable, 7.3 In Length, 0.12 LB/Ea
Weight per unit	0.1200 (lbs/each)
Product Category	Integrated Non-Ballasted Lamps

Features

Base	GX23
lumens	825 MILS
Voltage Rating	ELBOW FITTING, 316 STAINLESS STEEL MATERIAL; 1/2 INCH SIZE A; 1/2 INCH SIZE B; .5 SIZE A - DECIMAL; .5 SIZE B - DECIMAL; 1/2 SIZE A - FRACTIONAL; 1/2 SIZE B - FRACTIONAL; NUCLEAR, PHARMACEUTICAL INDUSTRY CHEMICAL, PETROCHEMICAL APPLICATION; CAST PROCESS

Material, Color, and Finish

color rendering index (cri)	82 W
-----------------------------	------

Descriptions

Description	13W 2 PIN SINGLE TUBE BIAx GX23 4100K COMPACT
-------------	---

Manufacturer Information

GTIN	00043168975711
sub brand	Ecolux [®]
UPC	043168975711

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging


Carton	1
Package	10
Weight Per each	0.12



GE
Lighting

97571 - F13BX/841/ECO

GE Ecolux® Biax® T4 - Facilities; Retail Display; Hospitality; Office; Restaurant; Warehouse



CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
 - Remove and install by grasping only plastic portion of the lamp.

NOTES

- Based on 60Hz reference circuit.
- Fluorescent lamp lumens decline during life

GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Plug-In
Bulb	T4
Base	GX23
Equivalent Wattage	60.0 W
Rated Life	10000.0 hrs
Starting Temperature (MIN)	0.0 °C
LEED-EB MR Credit	423 picograms Hg per mean lumen hour
Additional Info	TCLP compliant
Primary Application	Facilities;Retail Display;Hospitality;Office;Restaurant;Warehouse

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	825.0
Mean Lumens	710.0
Nominal Initial Lumens per Watt	63
Color Temperature	4100.0 K
Color Rendering Index (CRI)	82.0

ELECTRICAL CHARACTERISTICS

Wattage	13.0
Voltage	120.0
Lamp Current	0.285 A
Current Crest Factor (MAX)	1.7
Supply Current Frequency	60.0 Hz

DIMENSIONS

Maximum Overall Length (MOL)	7.3000 in(185.4 mm)
Nominal Length	7.000 in(177.8 mm)
Base Face to Top of Lamp	6.690 in(169.9 mm)

PRODUCT INFORMATION

Product Code	97571
Description	F13BX/841/ECO
ANSI Code	60901-IEC-0013-1
Standard Package	BUNDLE
Standard Package GTIN	
Standard Package Quantity	100
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	100
UPC	043168975711