
GE Lighting

66649 - F34/CW/C/WM/ECO

F34/CW/C/WM/ECO-LFL - 30PK WITH UPC STICKERS ON L





GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T12
Base	Medium Bi-Pin (G13)
Rated Life	15000.0 hrs
Bulb Material	Sodalime glass
Starting Temperature (MIN)	15.0 °C
LEED-EB MR Credit	222 picograms Hg per mean lumen hour
Primary Application	Energy Saving

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	1800.0
Mean Lumens	1500.0
Nominal Initial Lumens per Watt	52
Color Temperature	4100.0 K
Color Rendering Index (CRI)	87.0

ELECTRICAL CHARACTERISTICS

Wattage	34.0

DIMENSIONS

Maximum Overall Length (MOL)	48.0000 in(1219.2 mm)
Nominal Length	48.000 in(1219.2 mm)
Bulb Diameter (DIA)	1.500 in(38.1 mm)

PRODUCT INFORMATION


Product Code	66649
Description	F34/CW/C/WM/ECO
Standard Package	Case
Standard Package GTIN	10043168666494
Standard Package Quantity	30
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	30
UPC	043168666497

GE Lighting

66649 - F34/CW/C/WM/ECO

F34/CW/C/WM/ECO-LFL - 30PK WITH UPC STICKERS ON L





GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T12
Base	Medium Bi-Pin (G13)
Rated Life	15000.0 hrs
Bulb Material	Sodalime glass
Starting Temperature (MIN)	15.0 °C
LEED-EB MR Credit	222 picograms Hg per mean lumen hour
Primary Application	Energy Saving

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	1800.0
Mean Lumens	1500.0
Nominal Initial Lumens per Watt	52
Color Temperature	4100.0 K
Color Rendering Index (CRI)	87.0

ELECTRICAL CHARACTERISTICS

Wattage	34.0

DIMENSIONS

Maximum Overall Length (MOL)	48.0000 in(1219.2 mm)
Nominal Length	48.000 in(1219.2 mm)
Bulb Diameter (DIA)	1.500 in(38.1 mm)

PRODUCT INFORMATION

Product Code	66649
Description	F34/CW/C/WM/ECO
Standard Package	Case
Standard Package GTIN	10043168666494
Standard Package Quantity	30
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	30
UPC	043168666497