



Product Number: 24827

Order Abbreviation: F48T12/CW/ECO

General Description: 39W, 48" MOL, T12 instant start Slimline fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI ECOLOGIC

*** Full Case Required**

Product Information

Abbrev. With Packaging Info.	F48T12CWECO 30/CS 1/SKU
Actual Length (in)	46.000
Actual Length (mm)	1168.40
Average Rated Life (hr)	9000
Base	Single Pin
Bulb	T12
Color Rendering Index (CRI)	60
Color Temperature/CCT (K)	4200
Diameter (in)	1.500
Diameter (mm)	38.10
Family Brand Name	Ecologic®
Industry Standards	ANSI C78.81 - 2001
Initial Lumens at 25C	2820
Mean Lumens at 25C	2482
Mean Lumens at 35C	2482
Nominal Length (in)	48.000
Nominal Length (mm)	1219.20
Nominal Wattage (W)	39.00



Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. operating cycles under specified conditions and with ballast meeting ANSI specifications. If operating cycle is increased, there will be a corresponding increase in the average hours life.
- Minimum starting temperature is a function of the ballast; consult the ballast manufacturer.
- SYLVANIA ECOLOGIC fluorescent lamps are designed to pass the Federal Toxic Characteristic Leaching Procedure (TCLP) criteria for classification as non-hazardous waste in most states. TCLP test results are available upon request. Lamp disposal regulations may vary, check your local & state regulations. For more information, please visit www.lamprecycle.org



Product Number: 24827

Order Abbreviation: F48T12/CW/ECO

General Description: 39W, 48" MOL, T12 instant start Slimline fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI ECOLOGIC

*** Full Case Required**

Product Information

Abbrev. With Packaging Info.	F48T12CWECO 30/CS 1/SKU
Actual Length (in)	46.000
Actual Length (mm)	1168.40
Average Rated Life (hr)	9000
Base	Single Pin
Bulb	T12
Color Rendering Index (CRI)	60
Color Temperature/CCT (K)	4200
Diameter (in)	1.500
Diameter (mm)	38.10
Family Brand Name	Ecologic®
Industry Standards	ANSI C78.81 - 2001
Initial Lumens at 25C	2820
Mean Lumens at 25C	2482
Mean Lumens at 35C	2482
Nominal Length (in)	48.000
Nominal Length (mm)	1219.20
Nominal Wattage (W)	39.00



Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. operating cycles under specified conditions and with ballast meeting ANSI specifications. If operating cycle is increased, there will be a corresponding increase in the average hours life.
- Minimum starting temperature is a function of the ballast; consult the ballast manufacturer.
- SYLVANIA ECOLOGIC fluorescent lamps are designed to pass the Federal Toxic Characteristic Leaching Procedure (TCLP) criteria for classification as non-hazardous waste in most states. TCLP test results are available upon request. Lamp disposal regulations may vary, check your local & state regulations. For more information, please visit www.lamprecycle.org