



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E50DT2 Top Push L/S Head *Eaton Corp*

Catalog Number	E50DT2
Manufacturer	Eaton Corp
Description	
Weight per unit	0.1100 (lbs/each)
Product Category	Limit Switch Heads

### Features

actuator	Adjustable spring return
dimensions	52.0700millimetreX39.1160millimetreX45.2120millimetre
environmental rating	NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
Material	Die Cast Zinc

### Descriptions

Description	TOP PUSH L/S HEAD
Product Type	E50 Heavy Duty Limit Switch

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113290607
Manufacturers Part Number	E50DT2
series	E50
UPC	782113290607

### Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
igcc	5219
Type	E50
unspsc code	39122221

### Packaging

Carton	1
Weight Per each	0.11

### Uses, Certifications, and Standards

Application	Automation And Logic Control Equipment
Operating Temperature	14° to 201°F (-10° to 94°C)
standard	UL Recognized; CSA Certified



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Limit Switch Body

E50DT2

UPC:782113290607

### Dimensions:

- **Height:** 1.78 IN
- **Length:** 2.05 IN
- **Width:** 1.54 IN

### Warranties:

- 1 year

### Specifications:

- **Actuator:** Adjustable spring return
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Operating Temperature:** 14° to 201°F (-10° to 94°C)
- **Series:** E50

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50DT2](#)

### Certifications:

- CSA Certified
- UL Recognized

**Product compliance:** No Data

