

Eaton E50KL25

Catalog Number: E50KL25

Eaton E50 NEMA heavy duty plug-in limit switch, Lever for Side Rotary Switches, Lever: Stainless Steel, Roller: Powdered Metal - Super Oilite enclosure



Photo is representative

General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch operator	E50KL25
	UPC
	782113308944
Product Length/Depth	Product Height
0.75 in	2.3 in
Product Width	Product Weight
1.24 in	0.06 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	Catalog Notes
UL Listed CSA Certified CE	Lever length is from the operating shaft axis to the roller axis

Type

Mechanical Limit Switches

Enclosure material

Roller: powdered metal-Super Oilite

Lever: stainless steel

Switch type

Lever for side rotary switches

Operating temperature - max

201 °F

Operating temperature - min

-40 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67, IP69K

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50KL25](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](#)

Eaton E50KL25

Catalog Number: E50KL25

Eaton E50 NEMA heavy duty plug-in limit switch, Lever for Side Rotary Switches, Lever: Stainless Steel, Roller: Powdered Metal - Super Oilite enclosure



Photo is representative

General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch operator	E50KL25
	UPC
	782113308944
Product Length/Depth	Product Height
0.75 in	2.3 in
Product Width	Product Weight
1.24 in	0.06 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	Catalog Notes
UL Listed CSA Certified CE	Lever length is from the operating shaft axis to the roller axis

Type

Mechanical Limit Switches

Enclosure material

Roller: powdered metal-Super Oilite

Lever: stainless steel

Switch type

Lever for side rotary switches

Operating temperature - max

201 °F

Operating temperature - min

-40 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67, IP69K

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50KL25](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](#)