



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E51KF723 Glass Fiber, Steel, Duplex, Straight, THD, 1/8 Bundle, 3 *Eaton Corp*

Catalog Number	E51KF723
Manufacturer	Eaton Corp
Description	Eaton E51 Series Glass Fiberoptic Cable, Forward Viewing, Fiberoptic, Sensor Distance: Depends On Controller Used, Stainless Steel Enclosure, Diffuse
Weight per unit	0.2500 (lbs/each)
Product Category	Sensor Cables

Features

dimensions	1.5000 IN X 0.3100 IN X 36.0000 IN
------------	------------------------------------

Descriptions

Description	GLASS FIBER,STEEL,DUPLEX,STRAIGHT,THD,1/8 BUNDLE,3
extra long description	ETN E51KF723 GLASS FIBER,SS,DUP,STR
Features	Eaton's E51 limit switch style modular sensors are available in thru-beam, reflex, polarized reflex, diffuse reflective and fiber optic sensing modes to solve a wide variety of sensing applications. Modular, plug-in components are easy to maintain, meaning less downtime and reduced inventory. Choose between 2-wire sensors with AC/DC operation and 4-wire sensors in either AC or DC styles. Connection options include terminal, mini-connector and various lengths of cable. Sensors can be ordered in component fo
Long Description	Eaton E51 Series Glass Fiberoptic Cable, Forward Viewing, Fiberoptic, Sensor distance: Depends on controller used, Stainless Steel enclosure, Diffuse
Product Type	Glass Fiber, SS, Dup, STR, THD, 1/8 Bu, 3'

Manufacturer Information

Brand	Eaton
GTIN	00782113209623
Manufacturers Part Number	E51KF723
UPC	782113209623

Taxonomies, Classifications, and Categories

Type	Limit switch photoelectric sensor accessory
------	---------------------------------------------

Packaging

Carton	1
Weight Per each	0.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Operating Temperature	-49° to 480°F (-45° to 249°C)
standard	UL Listed, CSA Certified