



Powering Business Worldwide

pe.eaton.com

Eaton Series C complete molded case circuit breaker

FD2020

UPC:786679312216

Dimensions:

- **Height:** 2.75 IN
- **Length:** 3.38 IN
- **Width:** 2.75 IN

Weight:3.15 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 20A
- **Interrupt Rating:** 65 kAIC at 240 Vac, 35 kAIC at 480 Vac
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 600 Vac, 250 Vdc
- **Trip Type:** Fixed thermal, fixed magnetic
- **Circuit Breaker Type:** FD
- **Circuit Breaker Frame Type:** Complete breaker
- **Frequency Rating:** 50/60 Hz
- **Frame Size:** F-frame
- **Series:** Series C
- **Terminals:** Load side

Supporting documents:

- [MOEM MCCB Product Selection Guide](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Time Current Curves for Series C® F-Frame Circuit Breakers](#)
- [FD2 3D Model Xchange](#)



- [F-frame Molded Case Circuit Breaker Drawing](#)
- [FD2 2D Drawing Xchange](#)
- [FD2 3D Inventor](#)
- [FD2 2D PDF](#)
- [Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)
- [Counterfeit and Gray Market Awareness Guide](#)
- [F-Frame 310+ Molded-case circuit breakers 15-225A](#)

Certifications:

- UL Listed

Product compliance: No Data



Powering Business Worldwide

pe.eaton.com

Eaton Series C complete molded case circuit breaker

FD2020

UPC:786679312216

Dimensions:

- **Height:** 2.75 IN
- **Length:** 3.38 IN
- **Width:** 2.75 IN

Weight:3.15 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 20A
- **Interrupt Rating:** 65 kAIC at 240 Vac, 35 kAIC at 480 Vac
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 600 Vac, 250 Vdc
- **Trip Type:** Fixed thermal, fixed magnetic
- **Circuit Breaker Type:** FD
- **Circuit Breaker Frame Type:** Complete breaker
- **Frequency Rating:** 50/60 Hz
- **Frame Size:** F-frame
- **Series:** Series C
- **Terminals:** Load side

Supporting documents:

- [MOEM MCCB Product Selection Guide](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Time Current Curves for Series C® F-Frame Circuit Breakers](#)
- [FD2 3D Model Xchange](#)



- [F-frame Molded Case Circuit Breaker Drawing](#)
- [FD2 2D Drawing Xchange](#)
- [FD2 3D Inventor](#)
- [FD2 2D PDF](#)
- [Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)
- [Counterfeit and Gray Market Awareness Guide](#)
- [F-Frame 310+ Molded-case circuit breakers 15-225A](#)

Certifications:

- UL Listed

Product compliance: No Data