



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E59M12C110A01A1 12MM Iprox Clone, Ac, Uns 1

Eaton Corp

Catalog Number	E59M12C110A01A1
Manufacturer	Eaton Corp
Description	Eaton Iprox Series Tubular Inductive Proximity Sensor Enclosure, 0.47 Dia, Sensor Dist 10 MM, 300 Ma Max Ac, 2 - Wire Ac, No, 300 Ma At 132 Vac, 3 Pin Dual Key Micro Connector, 20-132 Vac Input, <LT/> 3% Of Sensing Dist. Accuracy, Un-Shielded
Weight per unit	0.1000 (lbs/each)
Product Category	Inductive Proximity Sensor

Features

Accuracy	< 3% of sensing distance
connection	Connector
dimensions	0.4700 IN X 0.4700 IN X 2.7100 IN
media	Yes

Descriptions

Description	12MM IPROX CLONE,AC,UNS 1
extra long description	ETN E59-M12C110A01-A1 12MM IPROX CL
Features	These unique, adaptable, field-programmable sensors utilize exclusive SmartSense technology—featuring an embedded microprocessor—to perform special sensing functions at extended ranges. These capabilities include programmable attributes, such as sensing range, output types, contact types, response time and noise immunity. No other sensor on the market offers such extensive programmability.
Long Description	Eaton Iprox Series Tubular Inductive Proximity Sensor Enclosure, 0.47 dia, Sensor dist 10 mm, 300 mA max AC, 2 - Wire AC, NO, 300 mA at 132 Vac, 3 Pin Dual Key Micro Connector, 20-132 Vac input, <lt/> 3% of sensing dist. accuracy, Un-shielded
Product Type	12MM Iprox Clone, Ac, Uns 10MM SN, No Micro

Manufacturer Information

Brand	Eaton
GTIN	00782116183173
Manufacturers Part Number	E59-M12C110A01-A1
UPC	782116183173

Taxonomies, Classifications, and Categories

Type	Programmable inductive proximity sensor
------	---

Packaging

Carton	1
Weight Per each	0.1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Stationary Mach Equip In Factory - Other Stationary Machinery and Equipment - In Factory
environmental conditions	NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13, IP67, IP69K
standard	CSA Certified,UL Listed,CE Marked