



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

121 S 39th Ave #100
85009-0000, AZ Phoenix
Phone: 480-372-4901
Fax: 480-372-4902



FD3025 Type FD BRKR 3P 25A 600VAC Max 18K Aic *Eaton Corp*

Catalog Number	FD3025
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, FD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Three-Pole, 25 A, 600 Vac, 250 VDC, Load Side, 50/60 HZ
Weight per unit	4.3 (lbs/each)
Product Category	3 Pole

Features

Current Rating	25 A
dimensions	3.3800 IN X 4.1300 IN X 6.0000 IN
frame	F
Poles	3
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	TYPE FD BRKR 3P 25A 600VAC MAX 18K AIC
extra long description	ETN FD3025 TYPE FD BRK 3P 25A 600VA
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, FD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 25 A, 600 Vac, 250 Vdc, Load side, 50/60 Hz
Product Type	Type FD BRK 3P 25A 600VAC Max 18K Aic

Manufacturer Information

Brand	Eaton
GTIN	00786679305645
Manufacturers Part Number	FD3025
UPC	786679305645

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

121 S 39th Ave #100
85009-0000, AZ Phoenix
Phone: 480-372-4901
Fax: 480-372-4902

Packaging

Carton	1
Weight Per each	4.3499

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
standard	UL Listed