



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2260 N Burton Ave Suite 100  
65803-0000, MO Springfield  
Phone: 417-429-1665  
Fax: 417-429-1666



## ECLK518 1-1/2X18 LT Flex Coupling

*Crouse-Hinds*

Catalog Number	ECLK518
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Eclk Coupling, 18" Flexible Length, Male Connection One End, Female Connection One End, Forged Brass, 1-1/2" Trade Size
Weight per unit	14.1 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Female Union X Male Threaded
dimensions	24.6300 IN X 3.5000 IN X 3.5000 IN
outside diameter	3-1/2

### Dimensions and Weight

Length	18
--------	----

### Descriptions

Description	1-1/2X18 LT FLEX COUPLING
extra long description	CRS-H ECLK518 1-1/2 X 18 DIV 1 FLEX
Features	Crouse-Hinds series EC explosionproof couplings are used in hazardous areas where a flexible member is required in a conduit system to accomplish difficult bends, or to allow for movement or vibration of connected equipment or units.
Long Description	Eaton Crouse-Hinds series ECLK coupling, 18" flexible length, Male connection one end, female connection one end, Forged brass, 1-1/2" trade size
Product Type	1-1/2 X 18 Div 1 Flex CPLG Male-Female
Special Features	Liquidtight

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274263403
Manufacturers Part Number	ECLK518
UPC	782274263403

### Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	COUPLING

### Trade Size

Trade Size	1-1/2 in
------------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2260 N Burton Ave Suite 100  
65803-0000, MO Springfield  
Phone: 417-429-1665  
Fax: 417-429-1666

## Packaging

Carton	1
Weight Per each	14.1

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure standard	Class I Div 1 Group C D, Class II Div I Group E F G, Class III UL 1203