

Product specifications

AMPERAGE RATING	200 A
VOLTAGE RATING	240 Vac, 125 Vdc
TRIP TYPE	T186
CIRCUIT BREAKER TYPE	ED
CIRCUIT BREAKER FRAME TYPE	Complete breaker
SERIES	Series C
TERMINALS	Line and load
FRAME	F
FREQUENCY RATING	50 to 60 Hz
INTERRUPT RATING	65 kAIC at 240 Vac
NUMBER OF POLES	Two-pole

Resources

	Application of Tap Rules to Molded Case Breaker Terminals
	UL listed 100%-rated molded case circuit breakers
	Application of Multi-Wire Terminals for Molded Case Circuit Breakers
APPLICATION NOTES	Motor protection circuit breakers product aid
	StrandAble terminals product aid
	Current limiting Series C molded case circuit breakers product aid
	Multi-wire lugs product aid
BROCHURES	Power metering and monitoring with Modbus RTU product aid
	Circuit breaker motor operators product aid
	Plug-in adapters for molded case circuit breakers product aid
	Breaker service centers
CATALOGS	Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2
MULTIMEDIA	Circuit Breakers Explained
	Circuit breakers explained
	Eaton Specification Sheet - ED2200L
	Series C F-Frame molded case circuit breakers
SPECIFICATIONS AND DATASHEETS	Series C G-Frame molded case circuit breakers time current curves
	MOEM MCCB product selection guide
	Series C J-Frame molded case circuit breakers time current curves

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton ED2200L

Eaton Series C complete molded case circuit breaker, Series C, F-frame molded case circuit breaker, 200 A, Two-pole, Line and load terminals, Fixed thermal magnetic trip, ED breaker, 65 kAIC at 240 Vac

General specifications

PRODUCT NAME	Eaton Series C complete molded case circuit breaker
CATALOG NUMBER	ED2200L
UPC	786679454060
PRODUCT LENGTH/DEPTH	3.38 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	2.9 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
PRODUCT TYPE	Molded case circuit breaker



Powering Business Worldwide

Product specifications

AMPERAGE RATING	200 A
VOLTAGE RATING	240 Vac, 125 Vdc
TRIP TYPE	T186
CIRCUIT BREAKER TYPE	ED
CIRCUIT BREAKER FRAME TYPE	Complete breaker
SERIES	Series C
TERMINALS	Line and load
FRAME	F
FREQUENCY RATING	50 to 60 Hz
INTERRUPT RATING	65 kAIC at 240 Vac
NUMBER OF POLES	Two-pole

Resources

	Application of Tap Rules to Molded Case Breaker Terminals
	UL listed 100%-rated molded case circuit breakers
	Application of Multi-Wire Terminals for Molded Case Circuit Breakers
APPLICATION NOTES	Motor protection circuit breakers product aid
	StrandAble terminals product aid
	Current limiting Series C molded case circuit breakers product aid
	Multi-wire lugs product aid
BROCHURES	Power metering and monitoring with Modbus RTU product aid
	Circuit breaker motor operators product aid
	Plug-in adapters for molded case circuit breakers product aid
	Breaker service centers
CATALOGS	Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2
MULTIMEDIA	Circuit Breakers Explained
	Circuit breakers explained
	Eaton Specification Sheet - ED2200L
	Series C F-Frame molded case circuit breakers
SPECIFICATIONS AND DATASHEETS	Series C G-Frame molded case circuit breakers time current curves
	MOEM MCCB product selection guide
	Series C J-Frame molded case circuit breakers time current curves

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

