



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

217 Innovation Way
37075-0000, TN Hendersonville
Phone: 615-991-2399
Fax: 000-000-0000



EREWTRDM24 DBL Remote RND Emgcy Head WHT

Lithonia Lighting - Acuity

Catalog Number	EREWTRDM24
Manufacturer	Lithonia Lighting - Acuity
Description	The Lithonia Lighting® Ere Led Remotes Are Suitable For Indoor Lighting Applications, For Use As Part Of An Emergency Lighting System, Illuminating The Path Of Egress. These Twin Led Lamp Remotes Are Fully Adjustable and Are Suitable For Wall or Ceiling Mounting.
Weight per unit	1.0 (lbs/each)
Product Category	Emergency Lighting

Features

average life	100,000
Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
lumens	150 LM
Material	Thermoplastic
Maximum Operating Temperature	40
Power Source	Hardwired
Shape	Round
Warranty	2

Material, Color, and Finish

Color	White
color temperature	5000
Finish	Matte
Lens Color	Clear
Lens Material	Plastic

Dimensions and Weight

Height	2.5
Length	7
Width	5.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

217 Innovation Way
37075-0000, TN Hendersonville
Phone: 615-991-2399
Fax: 000-000-0000

Descriptions

Construction	New Construction,Remodel
Description	DBL REMOTE RND EMGCY HEAD WHT
extra long description	LITH ERE W T RD M24 Remote, White,
Long Description	The Lithonia Lighting® ERE LED Remotes are suitable for indoor lighting applications, for use as part of an emergency lighting system, illuminating the path of egress. These twin LED lamp remotes are fully adjustable and are suitable for wall or ceiling mounting.
Product Type	Remote Light Head

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00191848036716
Manufacturers Part Number	ERE T M24
UPC	191848036716

Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
----------------------	---------------------------

Packaging

Carton	1
Package	24
Weight	0.75
Weight Per each	1

Uses, Certifications, and Standards

Application	Education,Hospitality,Offices & Banks,Retail
environmental conditions	Indoor
Mounting	SURFACE
standard	C-UL-US,NFPA 101,NFPA 70,UL