

LED WALL PACK SERIES

WP - 30 Watts

PAGE 1 OF 1

Key Features & Benefits:

- Rugged Die Cast Aluminum Housing:
- Dark bronze polyester powder coat finish
- Optical Grade PolycarbonateLens:
- UV stabilized
- Molded prismatic for optimal uniformity
- Impact resistant
- · Continuous Gasket for Weather-Tight Seal
- LEDs Mounted to and Protected by Aluminum Housing with Easy Driver Access Hinged Door
- (3) 3/4" Threaded knockouts:
- (1) On back
- (1) On either side
- Suitable for Wet Locations
- 10 Year Limited Warranty
- · Mounting Options:
- Direct to electrical box
- Flush wall mount







Notes:









Technical Specifications:

Power: 30 Watts


Lumen Output: Up to 3,400 Lumens Efficacy (Im/W): Up to 113 Lumens per Watt


Kelvin: 4000K, 5000K

CRI: >80

Input Voltage: 120-277 VAC Life Span: 50,000 Hours


Operating Temperature: -40°F - 104°F Dimensions (LxWxD): 14.21" x 9.25" x 7.4"





ITEM#	WATTS	LUMEN OUTPUT	EFFICACY (Im/W)	KELVIN	DLC QPL CODE
ESL-WP-30W-240	30W	3,306	101	4000K	PWS4MG56
ESL-WP-30W-250	30W	3,400	113	5000K	PAFTZW91

Ordering Guide:



Options (Add as Suffix):

ESL-WP-PC (Wall Pack Photocell for 30W-135W Wall Packs)

ESL-4OCC (Occupancy Sensor, 0-10v Dimming, 8'-20' Mounting for 30W-135W Wall Packs)

ESL-REM-101 (Remote control to self program 4OCC Sensor for 30W-135W Wall Packs)

ESL-EMG-FDC-9.5W (Internal Emergency Backup 1,100 Lumens for the 30W Wall Pack, Factory Installed)

ESL-EMG-AC-18W (External Emergency Backup 1,980 Lumens, Field Remote Mounted)