

Eaton EVICX2301

Catalog Number: EVICX2301

Eaton Crouse-Hinds series EVI light fixture, Medium base, Heat and impact resistant glass globe, With cast copper-free alum guard, Incandescent, Copper-free aluminum, PS-25 max. lamp size, Ceiling mount, Factory sealed, 3/4", 120 Vac, 300W



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series EVI light fixture	EVICX2301
	UPC
	782274235851
Product Length/Depth	Product Height
7.25 in	13.75 in
Product Width	Product Weight
7.25 in	13 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Zone 1

Class I, Zone 2

Class II, Division 1

Class III

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Lamp type

Incandescent

Base type

Medium

Wattage

300W

Mounting Method

Ceiling

Trade size

3/4"

Guard type

With cast guard

Material

Copper-free aluminum

Globe material

Heat and impact resistant glass

Guard material

Copper-free aluminum

Voltage rating

120 Vac

Lamp size - max

PS-25

Special features

Factory sealed

Resources

Catalogs

[EVI Explosionproof Incandescent Light Fixtures catalog page](#)

Certification reports

[EVI Explosionproof Incandescent Light Fixtures UL certification](#)

[EVI Explosionproof Incandescent Light Fixtures UL certification \(Marine\)](#)

[EVI Explosionproof Incandescent Light Fixtures Canadian certification](#)

Installation instructions

[IF 1452 - EVI Explosionproof Incandescent Light Fixtures](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia