



GD2029, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GD2029](#)



Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 3" to 3-1/2" Rod, 3" Pipe.

Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

General

EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GD
U Bolt Type	258
UPC	781810260395
UPC 12 Digit	7818102603955

Dimensions

Dimension - B Length inch	1.50 in
Dimension - Height fraction	5-5/8 in
Dimension - Height inch	5.63 in
Dimension - Width fraction	4-7/8 in
Dimension - Width inch	4.81 in
Dimension - Width mm	122 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	3
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Tube Std Size	3
Conductor - Copper Tube Std Size Range	3

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - GD2029_MODEL-STEP](#)
- [3D Models - GD2029_MODEL-IGES](#)
- [3D Models - GD2029_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD..013775-01](#)



A proud member of the Hubbell Family.

