


ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1612 E. Booth Road 72143-0000, AR Searcy Phone: 501-368-0309





GFEP220 Type BR 30 Ma GFI BRKR 20A/2 Pole 120/240V 10K Eaton Corp

m	
Catalog Number	GFEP220
Manufacturer	Eaton Corp
Description	Eaton BR Gfci Circuit Breaker, Industrial Ground Fault Thermal-Magnetic Equipment Protector, 20 A, 10 Kaic, Two-Pole 120/240 V, Gfep, Common, #14-4 Awg, Ground Fault Circuit Interrupter, GFI
Weight per unit	0.8000 (lbs/each)
Product Category	20090324154445
Features	
dimensions	5.7500 IN X 3.0000 IN X 4.5000 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V
Descriptions	
Description	TYPE BR 30 MA GFI BRKR 20A/2 POLE 120/240V 10K
extra long description	ETN GFEP220 BR 30 mA GFI 20A/2 Pole
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR GFCI circuit breaker, Industrial ground fault
	thermal-magnetic equipment protector, 20 A, 10
	kAIC,Two-pole,120/240 V,GFEP,Common,#14-4 AWG,Ground
Des dust Turks	fault circuit interrupter,GFI
Product Type	BR 30 Ma GFI 20A/2 Pole 120/240V 10K
Manufacturer Information	
Brand	Eaton
GTIN	00786676382458
Manufacturers Part Number	GFEP220
UPC Taxonomies, Classifications, and C	786676382458

Taxo

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers



standard

ELLIOTT ELECTRIC SUPPLY 1612 E. Booth Road 72143-0000, AR Searcy Phone: 501-368-0309 Fax: 501-368-0619

1
10
0.8
OtherGeneration - Renewable Energy - Alternative
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine
Vessels and Equipment - Marine Vessels and Equipment -
OtherGeneration - Conventional Energy - Conventional Energy

UL 489