



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2703 Hancock Dr.
76504-0000, TX Temple
Phone: 254-899-2800
Fax: 254-899-2805



EWZ103 Astro Digital Timer DPST

Nsi Industries

Catalog Number	EWZ103
Manufacturer	Nsi Industries
Description	Astro Digital Timer DPST
Weight per unit	1.6 (lbs/each)
Product Category	Electronic Time Switches

Features

action	DPST
Base	Screw
Contact Rating	120-277 VAC
Phase	Single Phase
Poles	2
Timing Range	7 DAY

Dimensions and Weight

Size	L=5.062 - H=8.312 - W=3.062
------	-----------------------------

Descriptions

Description	ASTRO DIGITAL TIMER DPST
extra long description	TORK EWZ103 Astronomic 7-Day Digital
Features	Tork 7 Day 1 Channel DPST Astronomic Time Switch APPLICATIONS: Outdoor Signs Heating and Air Conditioning Lighting Security FEATURES: INPUT SUPPLY: 120-277 VAC 50/60Hz INPUT VOLTAGE: 120-277 VAC 50/60Hz OUTPUT DRY CONTACTS: DPST POWER CONSUMPTION: 6VA Max. TIMING ACCURACY: Line Frequency SCHEDULING: 20 ON/OFF set points repeat each day. Minimum Setting 1 minute. NO. OF CHANNELS: 1 Channel DAYLIGHT SAVINGS: Automatic adjustment (can be omitted) ASTRONOMIC: Adjustable 10 degrees - 60 degrees Northern or Sout
Long Description	Astro Digital Timer DPST
Product Type	Astronomic 7-Day Digital Time Switch One Channel 30A 120-277
Special Features	20 On-Off Set Points - Daylight Savings Auto - Leap Year Automatic Compensation

Manufacturer Information

Brand	TORK
GTIN	00786261824738
Manufacturers Part Number	EWZ103
UPC	786261824738



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2703 Hancock Dr.
76504-0000, TX Temple
Phone: 254-899-2800
Fax: 254-899-2805

Taxonomies, Classifications, and Categories

Category Description	TIMERS
Type	7 Day Astronomic Time Switch - 1 Or 2 Channel

Packaging

Carton	1
Weight Per each	1.552

Uses, Certifications, and Standards

Application	NSI
Enclosure environmental conditions	NEMA 3R Plastic Indoor-Outdoor With Locking Hasp -40 to + 149 F
Frequency Rating	50-60 Hz
Mounting	Screw Mount
Operating Temperature standard	-40 to + 149 F cULus